

CyAn ADP Configuration

	Mirror	Filter	Fluorochrome Examples	Detector
488 20mW	95/5	488/10	SSC	
		530/40	FITC, AF488, GFP, CFSE	FL1
	545LP	575/25	PE, DsRed	FL2
	595LP	613/20	PE-TXrd, PI	FL3
	640LP	680/30	PE-Cy5, PerCP, 7AAD, PE-Cy5.5	FL4
	730LP	750LP	PE-Cy7, PE-AF750	FL5
405 25mW		450/50	PB, LD Violet, DAPI	FL6
	485LP	560/80	PO	FL7
635 60mW	650LP	665/20	APC, AF647, To-Pro-3	FL8
	730LP	750LP	APC-Cy7, APC-AF750	FL9

